



Mission Critical Metallics®

ATI Titanium 6Al-4V ELI Alloy

GENERAL

ATI Ti-6Al-4V ELI alloy (Extra Low Interstitials, UNS R56401) is a higher purity grade of ATI Ti-6Al-4V alloy. This grade has lower oxygen, carbon, and iron content. It is used in biomedical applications such as surgical instruments, orthopedic implants, and is the preferred grade for marine and cryogenic applications, and some important aerospace components.

This titanium grade is produced by vacuum arc primary melting followed by a second vacuum arc remelting operation.

SPECIFICATIONS

- AMS 4930 - Bar, Wire, Billet, and Rings (annealed)
- AMS 4931 - Bar, Billet, and Rings
- AMS 4996 - Billet
- ASTM F 136 - Surgical Implants

PHYSICAL PROPERTIES

Melting Range: 2,800-3,000° F (1,538 - 1,649° C)

Density: 0.160 lbs/cu. in. ; 4.47 gm/cc

Beta Transus Temperature: 1,790° F (± 25°); 976.7° C (± 3.9°)

HEAT TREATMENT

ATI Ti-6Al-4V ELI alloy is normally used in the annealed condition.

1. Anneal: 1,300 -1,350° F; (704.4 - 732.2° C), 1 to 8 hours, air cool
2. Stress Relieving: 900 -1,200° F; (482.2 - 648.9° C), 1 to 4 hours, air cool

HARDNESS

Typical hardness in the annealed condition is Rockwell C 30-34.

FORGEABILITY/ FORMABILITY

ATI Ti-6Al-4V ELI alloy is finish forged from 1,750° F; (954.4° C) with a finishing temperature of 1,450° F; (787.8° C). Minimum reductions of 35% are recommended to obtain optimum properties.

The formability of ATI Ti-6Al-4V ELI alloy is better than standard grade ATI Ti-6Al-4V alloy, although it is still difficult to form at room temperature in the annealed condition. Severe forming operations such as bending or stretching can be performed on annealed material at temperatures up to 1,200° F; (648.9° C) without affecting mechanical properties. Hot sizing or shaping can be done by creep forming in the 1,000 -1,200° F; (537.8 - 648.9° C) temperature range.

MACHINABILITY

ATI Ti-6Al-4V ELI alloy can be machined using practices for austenitic stainless steels using slow speeds, heavy feeds, rigid tooling, and large amounts of non-chlorinated cutting fluid.

WELDABILITY

ATI Ti-6Al-4V ELI alloy is easily welded in the annealed condition.

Precautions must be taken to prevent oxygen, nitrogen, and hydrogen contamination. Fusion welding can be done in inert gas filled chambers or using inert gas welding of the molten metal and the adjacent heated zones using a trailing shield. Spot, seam, and flash welding can be performed without resorting to protective atmospheres.

Properties of ATI Ti-6Al-4V ELI alloy welds such as ductility, impact strength and fracture toughness are significantly better than welds of standard grade ATI Ti-6Al-4V alloy.

SPECIAL PRECAUTIONS

ATI Ti-6Al-4V ELI alloy can be subject to hydrogen contamination during improper pickling and by oxygen, nitrogen, and carbon pickup during forging, heat treating, brazing, etc. This contamination results in a deterioration in ductility which could adversely effect notch sensitivity and forming characteristics.


Data are typical and should not be construed as maximum or minimum values for specification or for final design. Data on any particular piece of material may vary from those herein. Copyright © ATI Allvac 2010. Allvac® is a registered trademark of ATI Properties, Inc.

ATI Allvac
2020 Ashcraft Ave., P.O. Box 5030
Monroe NC 28110-5030 USA
704-289-4511
www.allvac.com








ATI Titanium 6Al-4V ELI Alloy

Chemical Composition										
	N	C	H	O	Fe	Al	V	Ti	Other Elements	
% w/w, min.	-	-	-	-	-	5.50	3.50	-	-	
% w/w, max.	0.05	0.08	0.0125	0.13	0.25	6.75	4.50	Bal	0.30 Total 0.10 Each	



- Ultimate Tensile Strength
- 0.2% Yield Strength
- ▲ Reduction in Area
- ▼ Elongation
- Notched Tensile K_t=6.3



Data are typical and should not be construed as maximum or minimum values for specification or for final design. Data on any particular piece of material may vary from those herein. Copyright © ATI Allvac 2010. Allvac® is a registered trademark of ATI Properties, Inc.

ATI Allvac
 2020 Ashcraft Ave., P.O. Box 5030
 Monroe NC 28110-5030 USA
 704-289-4511
 www.allvac.com